




# MATERIAL SPECIFICATION & INSTALLATION GUIDE

## PRODUCT ITEM CODE & DESCRIPTION

**ML 4156 ~ CATHETER / IV HOOK**



## MATERIAL SPECIFICATION:

#304 Grade Stainless Steel, Surfaces #3 (Satin) Finish / Hook section (10mmØ)  
Welded to Mounting Plate (3mm thickness) / Exposed Fix (Counter sunk holes)

## DIMENSIONS:

Overall ~ 48mm W x 112mm H x 66mm D

## INSTALLATION:

1. May be subject to Australian Building Code Regulations or architectural plans for installation height, which is the responsibility of the installer.
2. Locate height requirement & mark on wall then drill fixing holes using mounting plate. Measure Twice/Drill Once .... ensuring no internal services fittings or fixtures are present such as electrical or plumbing.
3. It is recommended that the unit is installed whereby it clears any other fixtures by at least 100mm and that when fixing, it is secured using appropriate fasteners/anchors into studwork, noggings or suitable substrate support to ensure rigidity and longevity in application
4. Place a small amount of "wet area" rated silicone sealant to mounting plate rear surface, around the full perimeter (ensures rigid fitment), then secure to wall surface with appropriate counter sunk screws/wall-plugs (to be provided by the installer).
5. Clean off any excess silicone and leave to cure/set for at least 12 hours before use

**NOTE:** Not recommended for use with materials exceeding a gross weight of 20kg

*These units should only be installed by a competent tradesperson and Metlam Australia takes no responsibility for any damage to walls or fixtures due to incorrect installation.*