

MATERIAL SPECIFICATION & INSTALLATION GUIDE

PRODUCT ITEM CODE & DESCRIPTION

MLR 50 Series ~ PULL DOWN TOILET GRAB RAIL



MLR 50



MLR 50 NC (L/H in-situ depiction)

COMPONENT MATERIALS:

#304 Grade Stainless Steel 32mmØ x 1.2mmT Tubing, #3 Finish / Multi-point Fix Wall Mount Bracket / All Welds Seamless and Linished~Polished / *Can Also Be Provided in Bright Polished or Powder Cote Finish*

DIMENSIONS:

Grab Rail: 850mmL x 215mmH **Toilet Roll (where fitted):** 12.5mmØ Stainless Steel bar

Mounting Bracket: 104mmW x 315mmH x 30~50mmD x 2.5mmT

Mounting Holes: 7 off x 8mmØ

INSTALLATION:

These units are to be surface mounted and are subject to compliance to Australian Building Code Regulations and/or AS 1428.1 for height location and fitment for use as may be applicable, which is the responsibility of the installation contractor. Electrical components (Nurse Call Button - Not Included) must be installed by a suitably qualified tradesperson.

Anchors are not included with the units and are the responsibility of the installation contractor, as is the compliance re fitment of internal wall blocking, such as noggins for anchoring the unit to via appropriate hardware.

These units should only be installed by a competent tradesperson and Metlam Australia takes no responsibility for any damage to walls or fixtures due to incorrect installation.